

1 0833 | 2 0833 | 3 0000 | 4 | 5 | 6 | 7 | 8


SUPERSEDES 9245 274 44900 0833/000 p.190-1 Of 18/01/2011		HALOGEN LAMP INFRARED HeLeN 15009Z 1000W 235V				9245 274 44900 0833/000		19/09/2011	
REF. : PDM IRK 2011-016	DOCUMENTATION	UNIT mm	PROJ. EUROP 	2 SH	SH 190-1	10	1:1	A4	
NAME : J.P. CHARLIER		VALIDATION : A. PICHARD		DR. FISCHER Europe					
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.									

**PRODUCT REQUIREMENT SHEET**

See LV 75-032

<b>MEASURING VOLTAGE</b>	235V (stabilisation 3 min.)
<b>MEASURING POSITION</b>	Horizontal
<b>LIFE TEST POSITION</b>	Vertical
<b>BURNING POSITION</b>	Any
<b>SWITCHING CYCLE</b>	Continuous
<b>AGEING</b>	1h at rated voltage

	VALUE UNIT	TOLERANCE
<b>WATTAGE</b>	1000W	± 6 %
<b>LIFE</b>	5000 h	average
<b>COLOR TEMPERATURE</b> Clear lamp HeLeN Lamp	2500 K NA	± 100 K
<b>FLUX (HeLeN lamp)</b> Clear lamp Reduction	9000 lm 95 %	Indicative value min
<b>WEIGHT</b>	48 g	

1 0833	2 0833	3 0000	4	5	6	7	8	
SUPERSEDES : 9245 274 44900 0833/000 p. 190-2 Of 18/01/2011		HALOGEN LAMP INFRARED HeLeN 15009Z 1000W 235V			9245 274 44900 0833/000		19/09/2011	
REF. : PDM IRK 2011-016	DOCUMENTATION	UNIT mm	PROJ EUROP 	2 SH	SH	190-2	10	A4
NOM : J.P. CHARLIER	VALIDATION : A. PICHARD			DR. FISCHER Europe				
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.								